

TECHNICAL DATA SHEET

Silmer SH® 208-30Q

MQT Type Thiol Resin

#### **DESCRIPTION**

**Silmer® SH 208-30Q** is a silicon thiol resin with very high cross-link density. **Silmer SH 208-30Q** contains no dimethyl silicone groups to maximize the hardness of the materials cured from it.

### **TYPICAL PROPERTIES**

Appearance	Clear to slightly hazy liquid	
Viscosity, cPs	3,000	
Active Content, %	100	
SH content, %	14.6	
Odor	Distinctive but mild	

# **USES AND APPLICATION**

**Silmer SH 208-30Q** is designed to be the thiol component in a UV cured thiol-ene reaction based resin system. It can be reacted with vinyl containing crosslinked silicon Q resins, such as Silmer VQ92, and linear extenders such as Silmer VIN 65k as example systems.

Thiol-ene cured silicones are effective at providing very high elongation properties which are typical of condensation cured silicones but not of UV cured acrylate functional silicones. We have obtained elongation up to 200% with this family of products.

The formulation shown below was cured on the benchtop and also 3D printed. Due to the viscosity being too high for an SLA type printer, we instead used an UltiMaker 2+ FMD from Sturctra3D. This is a thermal cured printer so we attached a UV lamp to the print head or held the light by hand to affect UV curing.

**Silmer SH 208-30Q** can also be reacted in conditions in which any primary thiol would react. It is significantly sterically hindered but reacts quickly in our formulations.

#### **FORMULATION**

One of many formulations evaluated, the following formula gave good toughness and flexibility. The SH/Vinyl ratio should be 3.2 to 4.4; up to 17% of the **Silmer SH 208-30Q** is beneficial and up to 5% excess of Silmer VIN 65k can be used to improve tear strength.

Component	Charge	Properties after Cure	
Silmer SH 208-30Q	11%	Appearance	tough flexible, white opaque
Silmer 65K	55%	Tensile Strength (kPa)	3958
Silmer VQ 92*	34%	Elongation (%)	157
TPO-L	0.8%	Total Energy (J/m)	550
SH/VIN	3.2	Tear Strength (N/mm)	6.95
*delivered 1:1 in		Shore A Hardness	44
Silmer VIN 65k		G' (Pa)	4.7E+05
		G" (Pa)	3.5E+04
		Cure rate (Pa/s)	1.2E+05



Pictured above right are some bracelets 3D printed in the manner described above. Above left is a bat insignia being printed. The cured resins are opaque white, flexible and reasonably tough.

#### **SAFETY**

Before handling, read the Material Safety Data Sheet and container label for safe use, physical and health hazard information.

THIS MATERIAL IS NOT FOR MEDICAL OR DRUG USE.

# STORAGE AND SHELF LIFE

When stored in the original, unopened containers between 10 and  $40^{\circ}$ C, **Silmer SH 208-30Q** has a shelf life of 12 months from date of manufacture.

### **PACKAGING**

**Silmer SH 208-30Q** is available in 20kg and 200kg containers.

#### LEGAL DISCLAIMER

Siltech Corporation believes that the information in this technical data sheet is an accurate description of the typical uses of the product. Siltech Corporation, however, disclaims any liability for incidental or consequential damages, which may result from the use of the product that are beyond its control. Therefore, it is the user's responsibility to thoroughly test the product in their particular application to determine its performance, efficacy and safety. Nothing contained herein is to be considered as permission or a recommendation to infringe any patent or any other intellectual property right.

**SILMER**® is a registered trademark of Siltech Corporation, Toronto, Ontario, Canada.

©February 2020